

Compression Splice Conventional (Two Die) Full Tension

By FARGO
Catalog # TJA1808SSAC

Compression Splice, Conventional 2-Die, Full Tension , for
ACSS 477.0 kcmil 24/7



*Representative Image

Features

- For use with ACSS code name Flicker
- Full tension Splice assembly
- For use with HTJC Joint Compound sold separately

General

| | |
|--------------------|-----------------------------|
| Aluminum Die | 24AH |
| Compression Method | Conventional (2 die system) |
| EU RoHS Indicator | No |
| Inhibitor Loaded | No |
| Material | Aluminum; Steel |
| Press Minimum | 60 to |
| UPC | 096359470960 |

Dimensions

| | |
|---------------------------|----------|
| Diameter - Outside | 0.846 in |
| Length Before Compression | 29.32 in |
| Messenger Diameter Range | 0 - 0 |
| Weight | 3.500 lb |

Electrical Ratings

| | |
|---------------------|----------|
| Voltage Application | Standard |
|---------------------|----------|

Conductor Related

| | |
|---------------------------------|-----------------------|
| Conductor Compatibility | ACSS-Flicker-477-24/7 |
| Conductor Diameter (Main) Range | 0 - 0 |
| Conductor Type | ACSS |

Certifications and Compliance

| | |
|-----------|----|
| UL Listed | No |
|-----------|----|

Logistics

| | |
|-----------------|-----|
| Pallet Quantity | 180 |
|-----------------|-----|

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)