

Compression Splice Conventional (Two Die) Full Tension

By FARGO
Catalog # [TJA2208](#)

Compression Splice, Conventional 2-Die, Full Tension , for
ACSR 556.5 kcmil 24/7



*Representative Image

Features

- For use with ACSR code name Parakeet
- Full tension Splice assembly
- Joint Compound purchased separately

General

Aluminum Die	24AH
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	60 to
UPC	096359492030

Dimensions

Diameter - Outside	0.914 in
Length Before Compression	23.7 in
Messenger Diameter Range	0 - 0
Weight	2.744 lb

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSR-Parakeet-556.5-24/7
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	300
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)