

## Compression Splice Conventional (Two Die) Full Tension

By FARGO  
Catalog # [TJA2408](#)

Compression Splice, Conventional 2-Die, Full Tension , for  
ACSR 605.0 kcmil 24/7



\*Representative Image

### Features

- For use with ACSR code name Peacock
- Full tension Splice assembly
- Joint Compound purchased separately

### General

Aluminum Die	27AH
Compression Method	Conventional (2 die system)
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	60 to
UPC	096359452874

### Dimensions

Diameter - Outside	0.953 in
Length Before Compression	25.9 in
Messenger Diameter Range	0 - 0

### Electrical Ratings

Voltage Application	Standard
---------------------	----------

### Conductor Related

Conductor Compatibility	ACSR-Peacock-605-24/7
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR

### Certifications and Compliance

UL Listed	No
-----------	----

### Logistics

Pallet Quantity	135
-----------------	-----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)