

## Compression Splice Conventional (Two Die) Full Tension

By FARGO  
Catalog # TJA3321

Compression Splice, Conventional 2-Die, Full Tension , for  
ACSR 795.0 kcmil 54/7



\*Representative Image

### Features

- For use with ACSR code name Condor
- Full tension Splice assembly
- Joint Compound purchased separately

### General

Aluminum Die	30AH
Compression Method	Conventional (2 die system)
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	60 to
UPC	096359471455

### Dimensions

Diameter - Outside	1.092 in
Length Before Compression	27.9 in
Messenger Diameter Range	0 - 0

### Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

### Conductor Related

Conductor Compatibility	ACSR-Condor-795-54/7
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR

### Certifications and Compliance

UL Listed	No
-----------	----

### Logistics

Pallet Quantity	120
-----------------	-----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)