

Compression Splice Conventional (Two Die) Full Tension

By FARGO
Catalog # [TJA5624SSAC](#)

Compression Splice, Conventional 2-Die, Full Tension , for
ACSS 1510.5 kcmil 54/19



*Representative Image

Features

- For use with ACSS code name Parrot
- Full tension Splice assembly
- For use with HTJC Joint Compound sold separately

General

Aluminum Die	40AH
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	60 to

Dimensions

Diameter - Outside	1.505 in
Length Before Compression	42.12 in
Messenger Diameter Range	0 - 0

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACSS-Parrot-1510-54/19
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSS

Certifications and Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)