

Compression Splice Conventional (Two Die) Full Tension

By FARGO
Catalog # TJA5718

Compression Splice, Conventional 2-Die, Full Tension , for
ACSR 1590.0 kcmil 45/7



*Representative Image

Features

- For use with ACSR code name Lapwing
- Full tension Splice assembly
- Joint Compound purchased separately

General

Aluminum Die	40AH
Compression Method	Conventional (2 die system)
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	60 to
UPC	096359402251

Dimensions

Diameter - Outside	1.504 in
Length Before Compression	35.1 in
Messenger Diameter Range	0 - 0
Weight	14.000 lb

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACSR-Lapwing-1590-45/7
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	45
-----------------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)