

# Compression Splice Conventional (Two Die) Full Tension

By FARGO  
Catalog # [TJA6028](#)

Compression Splice, Conventional 2-Die, Full Tension , for  
ACSR 1780.0 kcmil 84/19



\*Representative Image

## Features

- For use with ACSR code name Chucker
- Full tension Splice assembly
- Joint Compound purchased separately

## General

Aluminum Die	42AH
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	100 to
UPC	096359568315

## Dimensions

Diameter - Outside	1.602 in
Length Before Compression	35.7 in
Messenger Diameter Range	0 - 0

## Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

## Conductor Related

Conductor Compatibility	ACSR-Chukar-1780-84/19
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR

## Certifications and Compliance

UL Listed	No
-----------	----

## Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)