



* Representative image

Single Bolt Aluminum Vise-Type Connector.

by FARGO
Catalog ID: GA9002GLSS

Single Bolt Aluminum Vise-Type Connector.

Product Details

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	240 lb/ft
Grommets	Yes
Inhibitor Loaded	Yes
Material	Aluminum Alloy
Material - Body	Aluminum Alloy
Material - Bolt	Stainless Steel
Material - Keeper	Aluminum Alloy
Material - Spacer	Aluminum
Plating	No
Product Category	Clamps
Style	Single Bolt
UPC	096359484790

Dimensions

Diameter - Bolt	0.38 in
Diameter - Bolt Head	0.56 in
Height	2.125 in
Length	1.125 in
Weight	0.24 lb
Width	1.875 in

Conductor Related

Conductor Diameter (Main) - Maximum	0.332 in
Conductor Diameter (Main) - Minimum	0.162 in
Conductor Diameter (Main) Range	0.162 - 0.332
Conductor Diameter (Tap) - Maximum	0.332 in
Conductor Diameter (Tap) - Minimum	0.076 in
Conductor Type	Aluminum/Copper

Certifications and Compliance

UL Listed

No

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com