



* Representative image

Grounding Clamp

by ANDERSON
Catalog ID: GC110162C

Grounding Clamp, Copper One-Three Cables to Rod or Tube, U-bolt style.
GROUND, BRZ BOLT, .365-.575 IN, 4.5 OD

- Everdur hardware supplied by adding Suffix ED

Product Details

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Material	Bronze
Material - Hardware	Stainless Steel
UPC	096359305583

Dimensions

Diameter - Clamping Hardware	4 in
Diameter - Rod / Tube	4 in
Diameter - Rod / Tube Outside	4.5 in
Weight	3.724 lb

Conductor Related

Conductor Diameter - Maximum	0.575 in
Conductor Diameter - Minimum	0.365 in
Conductor Diameter Range	0.365 - 0.575
Conductor Type	Copper

Logistics

Pallet Quantity	420 EA
-----------------	--------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsh@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com