



* Representative image

Connector, Vise-Type

by FARGO
Catalog ID: GC166P

Grounding Vise-Type Connector

- Side Opening Jaw facilitates easy installation.

Product Details

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	240 in-lbs
Cover Available	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Material - Keeper	Bronze
Plating	Yes
Product Category	Vise Type Connectors
UPC	096359307181

Dimensions

Bolt Diameter	0.250 in
Diameter - Bolt	0.25 in
Diameter - Bolt Head	0.31 in
Height	1.500 in
Length	1.000 in
Length - Nut Flat-To-Flat	0.38 in
Weight	0.176 lb
Width	0.875 in

Conductor Related

Conductor Diameter - Maximum	0.5 in
Conductor Diameter - Minimum	0.245 in
Conductor Diameter Range	0.245 - 0.5
Conductor Type	Messenger Wire

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems

210 N. Allen Centralia, MO 65240 USA

Phone: (573) 682-5521

Fax: (573) 682-8475

Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521

Fax: +1-573-682-8516

Email: hpsintlcs@hubbell.com