

Grounding Clamp

by FARGO
Catalog ID: GC5004P

Grounding Clamp, Copper Cable to Cable, Vice Type.

- Tin Plated.



* Representative image

Product Details

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	240 in-lbs
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Material - Keeper	Bronze
Plating	Yes
Product Category	Vise Type Connectors
UPC	096359307457

Dimensions

Diameter - Bolt	0.31 in
Diameter - Bolt Head	0.56 in
Height	1.250 in
Length	0.875 in
Weight	0.157 lb
Width	0.875 in

Conductor Related

Conductor Diameter (Ground Tap) - Maximum	0 in
Conductor Diameter (Ground Tap) - Minimum	0 in
Conductor Diameter (Main) - Maximum	0.232 in
Conductor Diameter (Main) - Minimum	0.128 in
Conductor Diameter (Tap) - Maximum	0.232 in
Conductor Diameter (Tap) - Minimum	0.128 in
Conductor Type	Copper
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com