



\* Representative image

## POLE EYE PLATE GUY ATTACHMENT, 21,000lbs RATED STRENGTH, 13/16in CLEVIS PIN HOLE, MOUNTS with THREE 3/4in BOLTS

by CHANCE Utility  
Catalog ID: GEP6N

Cast ductile iron pole eye plate for attaching to fiberglass guy strains or clevis fittings is rated for 20,000 lbs. at 45 and 90 degrees. Has 13/16" clevis hole and 13/16" upper and lower mounting holes as well as two 9/16" lag holes in the wide base. There are no cleats on back side, allowing for non-wood pole mounting. Common industry slang is Monkey Face.

- Wide base for stabilization
- Cast ductile iron per ASTM A-536
- galvanized per ASTM A-153

### Product Details

#### General

Coating	Galvanized, ASTM A-153
Material	Ductile Iron, ASTM A-536
UPC	096359511359

#### Dimensions

Distance From Pole	N/A
Weight	0.98 lb

#### Logistics

Pallet Quantity	480 EA
-----------------	--------

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscscs@hubbell.com](mailto:hpscscs@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)