



* Representative image

GP1210000S

by Acme Electric
Catalog ID: GP1210000S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 10kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	277/480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208/277 V
UL Insulation Class	180°C
UPC	047503001073
Winding Material	CU
kVA	10

Dimensions

Height	15.19 in
Length	10.84 in
Weight	125 lb
Width	13.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	277/480 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506