




GPT-750A

by CMC
Catalog ID: GPT-750A

TYPE: GPT / TC, Dual-Rated Solderless Aluminum Tap Connectors, For use with both aluminum and copper conductors, Cond. Range: Main: 750 kcmil - 500 kcmil, Tap: 750 kcmil - 1/0 AWG, 90° C Rated (486B Listed), UL Listed and CSA Certified. CMC® Parallel and Tee Taps are manufactured from high strength 6061-T6 aluminum alloy to insure both maximum strength and conductivity. They are dual rated for both copper and aluminum conductors and are electro tin plated to provide low contact resistance and protection against corrosion. Only a screddriver or allen wrench is needed for assembly. They are also reuseable.

- Supplied with tin-plated radial-tipped set-screws and tin plated for low contact resistance
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- CMC® recommends the use of an insulated Allen wrench.

Product Details

General

Material	Aluminum
UPC	192663023981

Dimensions

Height	2 in
Length	3.38 in
Width	1.5 in



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

