




GRP 101P-I-1.43R GF30 / NYLON 6 / BLACK

By Gleason Reel
Catalog # 101P-I-1.4



GRP 101P-I-1.43R GF30 / NYLON 6 / BLACK

Features

- Compact Design
- Non-Conductive
- Resists Corrosion

General

Color	Black
Material	Nylon 6
Series	PowerTrak GRP
Type	Standard Track

Dimensions

Bend (Radius)	1.43
Curve Length	1 ft
Height	1 in
Height - Window	0.75 in
Mounting Height	3.86 in
Pitch	1.25 in
Weight	0.2 lb
Width	1.03 in
Width - Window	0.59 in

Conductor Related

Diameter - Cable Outside	0.34 in
--------------------------	---------

Product Assets

- [Brochures - POWERTRAK® GRP Non-Metallic Cable/Hose Carrier](#)
- [Engineering Drawing - 101P1-14 .DXF Drawing](#)
- [Engineering Drawing - 101P1-14 .DWG Drawing](#)
- [Engineering Drawing - 101P1-14 .STP Drawing](#)
- [Installation Manuals - GRP Instructions - All Models 046823](#)
- [Installation Manuals - Cable/Hose Guidelines 043181](#)