



GRP 162P-3-3.44R GF20 / NYLON 6 / BLACK

By Gleason Reel
Catalog # 162P-III-3.4



GRP 162P-3-3.44R GF20 / NYLON 6 / BLACK

Features

- Standard Design
- Snap-Together Links
- Non-Conductive
- Resists Corrosion

General

Catalog Number	162P-III-3.4
Color	Black
Material	Nylon 6
Series	PowerTrak GRP
Type	Flip-Top Track

Dimensions

Bend (Radius)	3.44
Curve Length	1.5 ft
Height	1.62 in
Height - Window	1 in

Mounting Height	8.5 in
Pitch	1.81 in
Weight	0.74 lb
Width	4.02 in
Width - Window	3.08 in

Conductor Related

Diameter - Cable Outside	0.83 in
--------------------------	---------

Product Assets

- [Brochures - POWERTRAK® GRP Non-Metallic Cable/Hose Carrier](#)
- [Catalogs - Tool Assist Pro Ergonomic and Material Handling Products](#)
- [Catalogs - Entertainment](#)
- [Installation Manuals - Cable/Hose Guidelines 043181](#)
- [Installation Manuals - GRP Instructions - All Models 046823](#)
- [Specifications - 162PIII34](#)