



GRP 252P-I-4.78R GF20 / NYLON 6 / BLACK

By Gleason Reel
Catalog # [252P-I-4.7](#)



GRP 252P-I-4.78R GF20 / NYLON 6 / BLACK

Features

- Standard Design
- Snap-Together Links With Flip-Tops
- Vertical Separators Available

General

Color	Black
Material	Nylon 6
Series	PowerTrak GRP
Type	Flip-Top Track

Dimensions

Bend (Radius)	4.78
Curve Length	2 ft
Height	2.5 in
Height - Window	1.75 in
Mounting Height	12.06 in
Pitch	2.5 in
Weight	1 lb
Width	3.7 in
Width - Window	2.6 in

Conductor Related

Diameter - Cable Outside	1.46 in
--------------------------	---------

Product Assets

[Brochures - GLEASON_GRPtrak_BROCHURE](#)
[Installation Manuals - GRP Instructions - All Models 046823](#)
[Installation Manuals - Cable/Hose Guidelines 043181](#)
[Technical Solutions - GRD-252P-I-4.7-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
GRD-252P-I-4.7-SPEC-EN | REV 1/2024