



252P-IR-3.40 PowerTrak GRP

By Gleason Reel
Catalog # [252P-IR-3.4](#)

252P-IR-3.40 PowerTrak GRP



Features

- Standard design, Snap-together links with flip-tops

General

Series PowerTrak GRP
Type Flip-Top Track

Dimensions

Bend (Radius)	8.31 in
Curve Length	1.5 ft
Height	2.5 in
Height - Window	1.75 in
Mounting Height	9.3 in
Pitch	2.5 in
Weight	1 lb
Width	3.7 in
Width - Window	2.6 in

Conductor Related

Diameter - Cable Outside 1.46 in

Product Assets

[Brochures - GLEASON_GRPtrak_BROCHURE](#)
[Installation Manuals - GRP Instructions - All Models 046823](#)
[Installation Manuals - Cable/Hose Guidelines 043181](#)
[Technical Solutions - GRD-252P-IR-3.4-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
GRD-252P-IR-3.4-SPEC-EN | REV 1/2024