



# 55-4E-3DP-WL-40 Series 55 Limit Switch DPDT

By Gleason Reel  
Catalog # [55-4E-3DP-WL-40](#)

Series 55 Limit Switch DPDT



## Features

- Easy, precision timing adjustment using standard screwdriver and provided tool
- Industrial grade oil-impregnated bronze bearings
- Switch terminal screws for quick wiring
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

## General

Product Category	Limit Switches
Series	55
UPC	783246014368

## Dimensions

Circuits Normally Closed	3
Circuits Normally Open	3
Maximum Shaft Turns To Trip Contacts	90
Minimum Shaft Turns To Trip Contacts	3
Over Travel Shaft Turns	21
Reset Shaft Turns	2.5

## Certifications and Compliance

Nema Rating	4
-------------	---

## Product Assets

[Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)  
[Brochures - GLEASON\\_Series55\\_BROCHURE](#)  
[Engineering Drawing - Series 55 Rotary Limit Switch DXF](#)  
[Engineering Drawing - Series 55 Rotary Limit Switch DWG](#)  
[Installation Manuals - Limit Switch-Series 55 Adjustment and Maintenance Instruction 630535](#)  
[Technical Solutions - GRD-55-4E-3DP-WL-40-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
GRD-55-4E-3DP-WL-40-SPEC-EN | REV 1/2024