



55-4E-3SP-WB-111 Series 55 Limit Switch SPDT

By Gleason Reel
Catalog # [55-4E-3SP-WB-111](#)

Series 55 Limit Switch SPDT



Features

- Easy, precision timing adjustment using standard screwdriver and provided tool
- Industrial grade oil-impregnated bronze bearings
- Switch terminal screws for quick wiring
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

General

Product Category Limit Switches
Series 55

Dimensions

| | |
|--------------------------------------|------|
| Circuits Normally Closed | 3 |
| Circuits Normally Open | 3 |
| Maximum Shaft Turns To Trip Contacts | 97 |
| Minimum Shaft Turns To Trip Contacts | 2 |
| Over Travel Shaft Turns | 14 |
| Reset Shaft Turns | 1.25 |

Certifications and Compliance

Nema Rating 4

Product Assets

- [Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)
- [Brochures - GLEASON_Series55_BROCHURE](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DXF](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DWG](#)
- [Installation Manuals - Limit Switch-Series 55 Adjustment and Maintenance Instruction 630535](#)
- [Technical Solutions - GRD-55-4E-3SP-WB-111-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
GRD-55-4E-3SP-WB-111-SPEC-EN | REV 1/2024