



# 55-4E-4DP-WB-20-LD Series 55 Limit Switch DPDT

By Gleason Reel  
Catalog # [55-4E-4DP-WB-20-LD](#)

Series 55 Limit Switch DPDT



## Features

- Easy, precision timing adjustment using standard screwdriver and provided tool
- Industrial grade oil-impregnated bronze bearings
- Switch terminal screws for quick wiring
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

## General

Product Category                      Limit Switches  
Series    55

## Dimensions

|                                      |     |
|--------------------------------------|-----|
| Circuits Normally Closed             | 2   |
| Circuits Normally Open               | 2   |
| Maximum Shaft Turns To Trip Contacts | 182 |
| Minimum Shaft Turns To Trip Contacts | 4   |
| Over Travel Shaft Turns              | 40  |
| Reset Shaft Turns                    | 4   |

## Certifications and Compliance

|             |   |
|-------------|---|
| Nema Rating | 4 |
|-------------|---|

## Product Assets

- [Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)
- [Brochures - GLEASON\\_Series55\\_BROCHURE](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DXF](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DWG](#)
- [Installation Manuals - Limit Switch-Series 55 Adjustment and Maintenance Instruction 630535](#)
- [Technical Solutions - GRD-55-4E-4DP-WB-20-LD-SPEC-EN](#)



A proud member of the Hubbell Family.