



# 55-7E-4DP-WL-333 X-PRF Limit Switch

By Gleason Reel  
Catalog # [55-7E-4DP-WL-333](#)



Series 55 Explosion Proof Rotary Limit Switch

## Features

- Easy, precision timing adjustment using standard screwdriver and provided tool
- Industrial grade oil-impregnated bronze bearings
- Switch terminal screws for quick wiring
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

## General

Product Category                      Limit Switches  
Series    55

## Dimensions

Circuits Normally Closed	4
Circuits Normally Open	4
Maximum Shaft Turns To Trip Contacts	265
Minimum Shaft Turns To Trip Contacts	4
Over Travel Shaft Turns	48
Reset Shaft Turns	3.5

## Certifications and Compliance

Nema Rating                                      7/9

## Product Assets

- [Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)
- [Brochures - GLEASON\\_Series55\\_BROCHURE](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DXF](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DWG](#)
- [Installation Manuals - Limit Switch-Series 55 Explosion Proof](#)
- [Installation and Maintenance Instructions 63053507](#)
- [Technical Solutions - GRD-55-7E-4DP-WL-333-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
GRD-55-7E-4DP-WL-333-SPEC-EN | REV 1/2024