



55-4E-2DP-WR-111-LD Series 55 Limit Switch DPDT

By Gleason Reel

Catalog # [55-4E-2DP-WR-111-LD](#)

Series 55 Limit Switch DPDT



Features

- Easy, precision timing adjustment using standard screwdriver and provided tool
- Industrial grade oil-impregnated bronze bearings
- Switch terminal screws for quick wiring
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

General

Product Category	Limit Switches
Series	55

Dimensions

Circuits Normally Closed	2
Circuits Normally Open	2
Maximum Shaft Turns To Trip	192
Contacts	
Minimum Shaft Turns To Trip	3
Contacts	
Over Travel Shaft Turns	30
Reset Shaft Turns	2.5

Certifications And Compliance

Nema Rating	4
-------------	---

Product Assets

- [Brochures - Series 55 Rotary Limit Switches](#)
- [Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DWG](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DXF](#)
- [Installation Manuals - Limit Switch-Series 55 Adjustment and Maintenance Instruction 630535](#)



A Hubbell brand