



55-4E-3DP-WL-222-LD Series 55 Limit Switch DPDT

By Gleason Reel

Catalog # [55-4E-3DP-WL-222-LD](#)

Series 55 Limit Switch DPDT



Features

- Easy, precision timing adjustment using standard screwdriver and provided tool
- Industrial grade oil-impregnated bronze bearings
- Switch terminal screws for quick wiring
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

General

| | |
|------------------|----------------|
| Product Category | Limit Switches |
| Series | 55 |

Dimensions

| | |
|-----------------------------|-----|
| Circuits Normally Closed | 3 |
| Circuits Normally Open | 3 |
| Maximum Shaft Turns To Trip | 90 |
| Contacts | |
| Minimum Shaft Turns To Trip | 3 |
| Contacts | |
| Over Travel Shaft Turns | 21 |
| Reset Shaft Turns | 2.5 |

Certifications And Compliance

| | |
|-------------|---|
| Nema Rating | 4 |
|-------------|---|

Product Assets

- [Brochures - Series 55 Rotary Limit Switches](#)
- [Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DWG](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DXF](#)
- [Installation Manuals - Limit Switch-Series 55 Adjustment and Maintenance Instruction 630535](#)



A Hubbell brand