



# 55-4E-4DP-WL-80-LD Series 55 Limit Switch DPDT

By Gleason Reel  
Catalog # [55-4E-4DP-WL-80-LD](#)



Series 55 Limit Switch DPDT

## Features

- Easy, precision timing adjustment using standard screwdriver and provided tool
- Industrial grade oil-impregnated bronze bearings
- Switch terminal screws for quick wiring
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

## General

Product Category	Limit Switches
Series	55

## Dimensions

Circuits Normally Closed	4
Circuits Normally Open	4
Maximum Shaft Turns To Trip	182
Contacts	
Minimum Shaft Turns To Trip	4
Contacts	
Over Travel Shaft Turns	40
Reset Shaft Turns	4

## Certifications And Compliance

Nema Rating	4
-------------	---

## Product Assets

- [Brochures - Series 55 Rotary Limit Switches](#)
- [Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DWG](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DXF](#)
- [Installation Manuals - Limit Switch-Series 55 Adjustment and Maintenance Instruction 630535](#)



A Hubbell brand