



55-7E-2DP-WR-333 X-PRF Limit Switch

By Gleason Reel
Catalog # [55-7E-2DP-WR-333](#)



Series 55 Explosion Proof Rotary Limit Switch

Features

- Easy, precision timing adjustment using standard screwdriver and provided tool
- Industrial grade oil-impregnated bronze bearings
- Switch terminal screws for quick wiring
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

General

| | |
|------------------|----------------|
| Product Category | Limit Switches |
| Series | 55 |

Dimensions

| | |
|-----------------------------|-----|
| Circuits Normally Closed | 2 |
| Circuits Normally Open | 2 |
| Maximum Shaft Turns To Trip | 265 |
| Contacts | |
| Minimum Shaft Turns To Trip | 4 |
| Contacts | |
| Over Travel Shaft Turns | 48 |
| Reset Shaft Turns | 3.5 |

Certifications And Compliance

| | |
|-------------|-----|
| Nema Rating | 7/9 |
|-------------|-----|

Product Assets

- [Brochures - Series 55 Rotary Limit Switches](#)
- [Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DWG](#)
- [Engineering Drawing - Series 55 Rotary Limit Switch DXF](#)
- [Installation Manuals - Limit Switch-Series 55 Explosion Proof](#)
- [Installation and Maintenance Instructions 63053507](#)



A Hubbell brand