



## 55-7E-4SP-WR-333 55-7E-4SP-WR-333 X-PRF Limit Switch

By Gleason Reel

Catalog # [55-7E-4SP-WR-333](#)



Series 55 Explosion Proof Rotary Limit Switch

### Features

- Easy, precision timing adjustment using standard screwdriver and provided tool
- Industrial grade oil-impregnated bronze bearings
- Switch terminal screws for quick wiring
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

### General

Product Category	Limit Switches
Series	55

### Dimensions

Circuits Normally Closed	4
Circuits Normally Open	4
Maximum Shaft Turns To Trip	265
Contacts	
Minimum Shaft Turns To Trip	4
Contacts	
Over Travel Shaft Turns	48
Reset Shaft Turns	3.5

### Certifications And Compliance

Nema Rating	7/9
-------------	-----

### Product Assets

[Brochures - Series 55 Rotary Limit Switches](#)  
[Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)  
[Engineering Drawing - Series 55 Rotary Limit Switch DWG](#)  
[Engineering Drawing - Series 55 Rotary Limit Switch DXF](#)  
[Installation Manuals - Limit Switch-Series 55 Explosion Proof](#)  
[Installation and Maintenance Instructions 63053507](#)



A Hubbell brand