



55-7E-4SP-WR-80 55-7E-4SP-WR-80 X-PRF Limit Switch

By Gleason Reel
Catalog # 55-7E-4SP-WR-80



Series 55 Explosion Proof Rotary Limit Switch

Features

- Easy, precision timing adjustment using standard screwdriver and provided tool
- Industrial grade oil-impregnated bronze bearings
- Switch terminal screws for quick wiring
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

General

Catalog Number	55-7E-4SP-WR-80
Product Category	Limit Switches
Series	55
UPC	783246016591

Dimensions

Circuits Normally Closed	4
Circuits Normally Open	4

Maximum Shaft Turns To Trip Contacts	68
Minimum Shaft Turns To Trip Contacts	1.5
Over Travel Shaft Turns	12
Reset Shaft Turns	0.75

Certifications And Compliance

Nema Rating	7/9
-------------	-----

Product Assets

[Brochures - Series 55 Rotary Limit Switches](#)
[Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)
[Catalogs - Entertainment](#)
[Engineering Drawing - Series 55 Rotary Limit Switch DXF](#)
[Engineering Drawing - Series 55 Rotary Limit Switch DWG](#)
[Installation Manuals - Limit Switch-Series 55 Explosion Proof](#)
[Installation and Maintenance Instructions 63053507](#)
[Specifications - 557E4SPWR80](#)



A Hubbell brand