



ACA10435-BC Yellow Industrial Reel, UL Type 1, 35 Ft, #10/4 SJO, 30 A, 250 VAC

By Gleason Reel
Catalog # [ACA10435-BC](#)



Yellow Industrial Reel, UL Type 1, 35 Ft, #10/4 SJO, 30 A, 250 VAC

Features

Durable, Corrosion Resistant Cast Aluminum Construction,UL Type 1,Multi-Position Guide Arm can be mounted in two different positions,Positive Latch mechanism automatically maintains desired cord length,Ratchet Lock can be disengaged in field for constant tension applications

General

Cable Length	35 Ft
Cable Type	#10/4 SJO
Catalog Number	ACA10435-BC
UPC	ACA10435-BC

Electrical Ratings

Current / Amperage Rating	30 A
Voltage Rating	250 VAC

Conductor Related

Number Of Wires	4-Wire
-----------------	--------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Brochures - ACA Industrial & Industrial Weatherproof Cord Reels](#)
- [Engineering Drawing - MODEL ACA DIMS](#)
- [Engineering Drawing - 064461APP](#)
- [Engineering Drawing - 064460APP](#)
- [Engineering Drawing - HBLIMB](#)
- [Engineering Drawing - HBLI340PB](#)
- [Installation Manuals - PDS-2847](#)
- [Literature - Model ACA/ACC/Cat 6 Cord Reels Instructions for Changing Roller Guide Position](#)
- [Specifications - ACA10435BC](#)



A Hubbell brand