



ACA12325-DR20 Yellow Industrial Reel with Yellow Portable Outlet Box, GFCI Module and (1) 20A Duplex Receptacle, UL Type 1, 25 Ft, #12/3 SJO, 20 A, 250 VAC

By Gleason Reel
Catalog # [ACA12325-DR20](#)

Yellow Industrial Reel with Yellow Portable Outlet Box, GFCI Module and (1) 20A Duplex Receptacle, UL Type 1, 25 Ft, #12/3 SJO, 20 A, 250 VAC

Features

Durable, Corrosion Resistant Cast Aluminum Construction,UL Type 1,Multi-Position Guide Arm can be mounted in two different positions,Positive Latch mechanism automatically maintains desired cord length,Ratchet Lock can be disengaged in field for constant tension applications

General

Cable Length	25 Ft
Cable Type	#12/3 SJO
Catalog Number	ACA12325-DR20
UPC	ACA12325-DR20

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	250 VAC

Conductor Related



Number Of Wires	3-Wire
-----------------	--------

Logistics

Carton Quantity	1
Pallet Quantity	16

Product Assets

- [Brochures - ACA Industrial & Industrial Weatherproof Cord Reels](#)
- [Engineering Drawing - MODEL ACA DIMS](#)
- [Engineering Drawing - 064461APP](#)
- [Engineering Drawing - 064460APP](#)
- [Engineering Drawing - HBLIMB](#)
- [Engineering Drawing - HBLI340PB](#)
- [Installation Manuals - PDS-2847](#)
- [Literature - Model ACA/ACC/Cat 6 Cord Reels Instructions for Changing Roller Guide Position](#)
- [Specifications - ACA12325DR20](#)