



ACA12325-SR20 Yellow Industrial Reel with HBL5369C, UL Type 1, 25 Ft, #12/3 SJO, 20 A, 250 VAC

By Gleason Reel
Catalog # [ACA12325-SR20](#)

Yellow Industrial Reel with HBL5369C, UL Type 1, 25 Ft, #12/3 SJO, 20 A, 250 VAC

Features

Durable, Corrosion Resistant Cast Aluminum Construction,UL Type 1,Multi-Position Guide Arm can be mounted in two different positions,Positive Latch mechanism automatically maintains desired cord length,Ratchet Lock can be disengaged in field for constant tension applications

General

Cable Length	25 Ft
Cable Type	#12/3 SJO
Catalog Number	ACA12325-SR20
UPC	ACA12325-SR20

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC



Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Brochures - ACA Industrial & Industrial Weatherproof Cord Reels](#)
- [Engineering Drawing - 064461APP](#)
- [Engineering Drawing - HBLIMB](#)
- [Engineering Drawing - HBLI340PB](#)
- [Engineering Drawing - 064460APP](#)
- [Engineering Drawing - MODEL ACA DIMS](#)
- [Installation Manuals - PDS-2847](#)
- [Literature - Model ACA/ACC/Cat 6 Cord Reels Instructions for Changing Roller Guide Position](#)
- [Specifications - ACA12325-SR20](#)



A Hubbell brand