



ACA12335-SR20, Yellow Industrial Reel with HBL5369C, UL Type 1, 35 Ft, #12/3 SJO, 20 A, 250 VAC

By Gleason Reel
Catalog # [ACA12335-SR20](#)

Yellow Industrial Reel with HBL5369C, UL Type 1, 35 Ft, #12/3 SJO, 20 A, 250 VAC



General

Cable Length	35 Ft
Cable Type	#12/3 SJO
UPC	ACA12335-SR20

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Brochures - ACA Industrial & Industrial Weatherproof Cord Reels](#)
- [Engineering Drawing - 064461APP](#)
- [Engineering Drawing - HBLIMB](#)
- [Engineering Drawing - HBLI340PB](#)
- [Engineering Drawing - 064460APP](#)
- [Engineering Drawing - MODEL ACA DIMS](#)
- [Installation Manuals - PDS-2847](#)
- [Literature - Model ACA/ACC/Cat 6 Cord Reels Instructions for Changing Roller Guide Position](#)