



# ACA12345-DR20, Industrial Reel w/ Portable Outlet Box, GFCI Module and (1) 20A Duplex Receptacle

By Gleason Reel  
Catalog # [ACA12345-DR20](#)

Yellow Industrial Reel with Yellow Portable Outlet Box, GFCI Module and (1) 20A Duplex Receptacle, UL Type 1, 45 Ft, #12/3 SJO, 20 A, 125 VAC



## General

Cable Length	45 Ft
Cable Type	#12/3 SJO
UPC	ACA12345-DR20

## Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	125 VAC

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

[Brochures - ACA Industrial & Industrial Weatherproof Cord Reels](#)  
[Catalogs - Tool Assist Pro Ergonomic and Material Handling Products](#)  
[Engineering Drawing - 064461APP](#)  
[Engineering Drawing - HBLIMB](#)  
[Engineering Drawing - HBLI340PB](#)  
[Engineering Drawing - 064460APP](#)  
[Engineering Drawing - MODEL ACA DIMS](#)  
[Installation Manuals - PDS-2847](#)  
[Literature - Model ACA/ACC/Cat 6 Cord Reels Instructions for Changing Roller Guide Position](#)