



ACA16325-BC15 Yellow Industrial Reel, UL Type 1, 25 Ft, #16/3 SJO, 15 A, 250 VAC

By Gleason Reel
Catalog # [ACA16325-BC15](#)



Yellow Industrial Reel, UL Type 1, 25 Ft, #16/3 SJO, 15 A, 250 VAC

Features

Durable, Corrosion Resistant Cast Aluminum Construction,UL Type 1,Multi-Position Guide Arm can be mounted in two different positions,Positive Latch mechanism automatically maintains desired cord length,Ratchet Lock can be disengaged in field for constant tension applications

General

Cable Length	25 Ft
Cable Type	#16/3 SJO
Catalog Number	ACA16325-BC15
UPC	ACA16325-BC15

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	250 VAC

Voltage Rating Description	250 VAC
----------------------------	---------

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Product Assets

- [Brochures - ACA Industrial & Industrial Weatherproof Cord Reels](#)
- [Engineering Drawing - 064461APP](#)
- [Engineering Drawing - HBLIMB](#)
- [Engineering Drawing - HBLI340PB](#)
- [Engineering Drawing - 064460APP](#)
- [Engineering Drawing - MODEL ACA DIMS](#)
- [Installation Manuals - PDS-2847](#)
- [Literature - Model ACA/ACC/Cat 6 Cord Reels Instructions for Changing Roller Guide Position](#)
- [Specifications - ACA16325-BC15](#)