



# ACA-CAT6-L-BL, RJ45-Lift Cord Reel, Black

By Gleason Reel  
Catalog # [ACA-CAT6-L-BL](#)

ACA-CAT6/RJ45-LIFT CORD REEL-BLACK

## Features

- 50ft (15.24m) cord length, 4ft (1.22m) input pigtail
- Durable, corrosion resistant cast aluminum construction
- Black powder coat finish (primary color) - also available in yellow and white
- Movable guide arm can be mounted in horizontal payout and vertical lift positions
- Positive latch mechanism automatically maintains desired cord length
- Ratchet lock can be disengaged in field for constant tension applications
- Equipped with special gold-on-gold slip ring that maintains Ethernet communications with minimal electrical noise for unparalleled performance
- 1000BASE-T (Gigabyte Ethernet) compatible Plug-n-play Ethernet connection
- RJ45 plug on both input and output cords and vertical lift positions

## General

Cable Type                      Cat6



\*Representative Image

Catalog Number	ACA-CAT6-L-BL
Style	Cat 6
Type	Ethernet
UPC	783246021984

## Dimensions

Dimensions	10.00 in x 13.00 in x 15.00 in
Height	15 in
Length	10 in
Width	13 in

## Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

## Product Assets

[Brochures - Cat6 Data Reels](#)  
[Brochures - ACA Industrial & Industrial Weatherproof Cord Reels](#)  
[Installation Manuals - Model ACA/ACC Cord Reels Instructions for changing roller guide position](#)  
[Specifications - ACACAT6LBL](#)



A Hubbell brand