



ACA-CAT6-R-WH, RJ45 Retrieve Cord Reel, White

By Gleason Reel

Catalog # [ACA-CAT6-R-WH](#)

ACA-CAT6/RJ45-RETRIEVE-CORD REEL-WHITE



*Representative Image

Features

- 50ft (15.24m) cord length, 4ft (1.22m) input pigtail
- Durable, corrosion resistant cast aluminum construction
- Black powder coat finish (primary color) - also available in yellow and white
- Movable guide arm can be mounted in horizontal payout and vertical lift positions
- Positive latch mechanism automatically maintains desired cord length
- Ratchet lock can be disengaged in field for constant tension applications
- Equipped with special gold-on-gold slip ring that maintains Ethernet communications with minimal electrical noise for unparalleled performance
- 100BASE-T (Gigabyte Ethernet) compatible Plug-n-play Ethernet connection
- RJ45 plug on both input and output cords and vertical lift positions

General

Cable Type	Cat6
Style	Cat 6
Type	Ethernet
UPC	783246021991

Dimensions

Dimensions	10.00 in x 13.00 in x 15.00 in
Height	15 in
Length	10 in
Width	13 in

Product Assets

[Brochures - Cat6 Data Reels](#)

[Installation Manuals - Model ACA/ACC Cord Reels Instructions for changing roller guide position](#)



A Hubbell brand