



C50-F03-2301I-Z-S C50 CA TRLY 7.88L 3.12D 3.19WD

By Gleason Reel
Catalog # C50-F03-2301I-Z-S

C50 CA TRLY 7.88L 3.12D 3.19WD



Features

- Flat Clamp design
- Hardware is Zinc Plated
- 1.25" Dia Precision ball bearing steel wheels
- Max Trolley load =80Lbs
- Travel speed up to 350 fpm
- Max travel = 250ft

General

Accessories

- Tow Chains
- Hose - General Purpose Or Hydraulic
- Junction Box(es)
- Cable - Round Or Flat
- Terminal Blocks
- Ty-Wraps
- Cable Clamps-Flat Design
- Cable Glands For Single Cables Or Groups

Cable Type	Flat
Catalog Number	C50-F03-2301I-Z-S
Clamping Element Design	Flat Clamp
Material - Hardware	Zinc Plated Hardware
Series	C50
Type	Cable Trolley

Dimensions

Diameter - Saddle	3.12
Height - Window	2.3 in
Overall Length	7.88
Radius - Saddle	1.56
Width - Window	1.88 in

Product Assets

[Installation Manuals - C-Rail Festoon Installation Instructions 043574](#)
[Specifications - C50F032301I2S](#)



A Hubbell brand