



C50-F04-1305I-Z-S C50 CA TRLY

7.88L 4.94D 6.31WD

By Gleason Reel
Catalog # [C50-F04-1305I-Z-S](#)

C50 CA TRLY 7.88L 4.94D 6.31WD

Features

- Flat Clamp design
- Hardware is Zinc Plated
- 1.25" Dia Precision ball bearing steel wheels
- Max Trolley load =80Lbs
- Travel speed up to 350 fpm
- Max travel = 250ft

General

Accessories

- Tow Chains
- Hose - General Purpose Or Hydraulic
- Junction Box(es)
- Cable - Round Or Flat
- Terminal Blocks
- Ty-Wraps
- Cable Clamps-Flat Design
- Cable Glands For Single Cables Or Groups



Cable Type	Flat
Catalog Number	C50-F04-1305I-Z-S
Clamping Element Design	Flat Clamp
Material - Hardware	Zinc Plated Hardware
Series	C50
Type	Intermediate Trolley

Dimensions

Diameter - Saddle	4.94
Height - Window	1.38 in
Overall Length	7.88
Radius - Saddle	2.47
Width - Window	5 in

Product Assets

- [Installation Manuals - C-Rail Festoon Installation Instructions 043574](#)
- [Specifications - C50F041305I ZS](#)



A Hubbell brand