



C50-F06-0705T-Z-S C50 Tow Trolley

By Gleason Reel
Catalog # C50-F06-0705T-Z-S

C50 Tow Trolley

Features

- Flat Clamp design
- Hardware is Zinc Plated
- 1.25" Dia Precision ball bearing steel wheels
- Max Trolley load =80Lbs
- Travel speed up to 350 fpm
- Max travel = 250ft

General

Accessories

- Tow Chains
- Hose - General Purpose Or Hydraulic
- Junction Box(es)
- Cable - Round Or Flat
- Terminal Blocks
- Ty-Wraps
- Cable Clamps-Flat Design
- Cable Glands For Single Cables Or Groups



Oh No!
IMAGE COMING SOON

Cable Type	Flat
Catalog Number	C50-F06-0705T-Z-S
Clamping Element Design	Flat Clamp
Finish Type	Orange Baked Polyester Powder Finish
Material - Hardware	Zinc Plated Hardware
Series	C50
Type	Tow Trolley

Dimensions

Diameter - Saddle	6.31
Height - Window	0.7 in
Overall Length	7.88
Radius - Saddle	3.16
Width - Window	5 in

Product Assets

[Installation Manuals - C-Rail Festoon Installation Instructions 043574](#)
[Specifications - C50F060705TZS](#)



A Hubbell brand