



C60-F03-1105T-Z-S C60 Tow trolley

By Gleason Reel
Catalog # [C60-F03-1105T-Z-S](#)

C60 Tow trolley



Features

- Flat Clamp design
- Hardware is Zinc Plated
- 1.57" Dia Precision ball bearing steel wheels
- Max Trolley load =125Lbs
- Travel speed up to 450 fpm
- Max travel = 500ft

General

Accessories

- Cable Clamps - Flat Design
- Junction Box(es)
- Cable - Round Or Flat
- Terminal Blocks
- Ty-Wraps
- Hose - General Purpose Or Hydraulic
- Tow Chains
- Cable Glands For Single Cables Or Groups

Cable Type	Flat
Catalog Number	C60-F03-1105T-Z-S
Clamping Element Design	Flat Clamp
Finish Type	Orange Baked Polyester Powder Finish
Material - Hardware	Zinc Plated Hardware
Series	C60
Type	Tow Trolley

Dimensions

Diameter - Saddle	3.12
Height - Window	1.19 in
Overall Length	11.75
Radius - Saddle	1.56
Width - Window	5 in

Product Assets

[Installation Manuals - C-Rail Festoon Installation Instructions 043574](#)
[Specifications - C60F031105TZS](#)



A Hubbell brand