



# GCC12350-DR 50' 12/3 Industrial Duty Cord Reel w/Dual Receptacle

By Gleason Reel  
Catalog # [GCC12350-DR](#)

50' 12/3 Industrial Duty Cord Reel w/Dual Receptacle



## Features

- Heavy steel frame with baked-on polyester finish
- 48" pigtail with three prong plug
- Multi-position four roller cord guide and adjustable cord stop
- Complete with dual receptacle (GFCI)

## General

Application	Ceiling, wall or under bench mount
Catalog Number	GCC12350-DR
Product Category	Reels
Type	Dual Receptacle
UPC	783246000958

## Dimensions

Weight	44.2 lb
--------	---------

## Electrical Ratings

Current / Amperage Rating	15 A
Current Rating	15 A

## Conductor Related

Cord Length	50 ft
Number of Conductors	3
Wire Size	#12 AWG

## Certifications And Compliance

Industry Standard(s)	cULus
----------------------	-------

## Product Assets

[Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)  
[Brochures - ACA Industrial & Industrial Weatherproof Cord Reels](#)  
[Brochures - HUBBELL INDUSTRIAL DUTY GCC CORD REELS](#)  
[Installation Manuals - GC and GL Series Cord Reel Instructions 630483](#)



A Hubbell brand