



HWP-0475 Push n Place Portable Workstation

By Gleason Reel

Catalog # [HWP-0475](#)

Here's a way to maintain flexibility on the plant floor without sacrificing safety and productivity. The Hubbell Workplace Solutions Push 'n Place portable workstation rolls easily on four heavy-duty locking, swivel casters. Constructed of strong extruded aluminum rail, it measures 36" deep and 90" high, including casters. Frame is 44" wide o.c., perfect for under a 5' conveyor section or 60" bench. Tool bar is 60" long and can be fitted with splice angles to adjoin two or more units. Bin Bar, air manifold and balancer trolley with fitting plus 3/8" hose are standard. Frame is finished with beige baked polyester. Brackets are matte black. Assembly required. Workstation Accessories and Swing Arms may be added to further customize unit.

Features

- Portable workstation rolls easily on four heavy-duty locking, swivel casters, Frame is finished with beige baked polyester.
- Brackets are matte black

General

Catalog Number	HWP-0475
UPC	783246006448



Product Assets

[Brochures - ToolAssistPro Idea Book](#)
[Catalogs - Tool Assist Pro Ergonomic and Material Handling Products](#)
[Engineering Drawing - GLEASON_620321_HWP-0475](#)
[Installation Manuals - Push 'n Place Workstation Instructions 630331](#)
[Product Logo - ToolAssistPro-Logo](#)
[Specifications - HWP-0475](#)
[Video - Tool Assist Pro for material handling and ergonomics](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
GRD-HWP0475-SPEC-EN | REV 10/2024