



## K18751-6-1

By Gleason Reel  
Catalog # [K18751-6-1](#)

Gleason Series K Hose Reels are ideal for hydraulic hose control on boom cranes, hoists, tree cutters, lifts or any moving hydraulic equipment. They can also be used for other liquids or air. Whether machines push-pull, extend-retract, turn, tip, clamp hold or dump, Gleason series K all-steel spring driven dual hose reels speed operation and improve handling and safety. Series K Hose Reels handle up to 80 ft. of 1/4" I.D. dual hose with 3000 psi full-flow pressure throughout the reel. Maximum 3/4" I.D. hose.

### Features

- Dual port swivel joint removes easily when replacing seal
- Hose connections readily accessible
- Welded, all steel frame for maximum strength
- Pre-lubricated, sealed ball bearings

### General

Type Hydraulic Dual Hose



### Dimensions

Weight 120 lb

### Product Assets

[Brochures - GLEASON\\_UKHM\\_BROCHURE](#)

[Brochures - GLEASON\\_SeriesK\\_BROCHURE](#)

[Installation Manuals - K-Reel Hose Assembly Instructions 035254](#)

[Installation Manuals - K-Reel Seal Kit Instructions 032417](#)

[Installation Manuals - K-18 Reel Instructions 052761](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
GRD-K18751-6-1-SPEC-EN | REV 10/2023