



I115-M

By Gleason Reel

Standard Trolley Design, Flat, Round or Mixed Design, Max Saddle Dia 12.59", 450lbs, 500fpm



Features

- Crowned 2.48" steel wheels with side guide rollers
- Anti-lift rollers
- Sealed bearings are pre-lubricated for life
- Tow trolley included as standard
- Zinc plated hardware
- Orange baked polyester powder finish
- Heavy duty bumpers

Application

Overhead Cranes

General

Accessories

- Cable Clamps
- Ty-Raps
- Tow Chains
- Round Or Flat
- Hose

Application - For Use On
Available Options

Finish Type
Load Capacity
Maximum Acceleration
Plating
Series
Type

- Cable Glands For Single Cables Or Groups
 - Terminal Box
 - Terminal Blocks
 - Shock Cords
- Mixed Cable or Hose
Flat, Round or Mixed Cable/
Hose
Zinc Plated
450 lbs
2
Yes
I115-M
Standard Trolley Design

Product Assets

[Brochures - Beam·Master™ FESTOON SYSTEMS](#)
[Installation Manuals - I-Beam Festoon Instructions 043053](#)
[Specifications - I115-M](#)



A Hubbell brand