



WBL-204LED 48" LED Two Tube Adjustable Workstation Light

By Gleason Reel
Catalog # [WBL-204LED](#)



48" LED Two Tube Adjustable Workstation Light

Features

- 4,000 nominal lumens
- 54,000 hours at LED at L70 for reduced maintenance
- Up to 124 lumens per watt
- Mounts directly to WBL light supports
- 0-10V dimming, standard
- Frosted acrylic lens
- Wide range of applications
- Universal voltage (120 - 277V)
- 80+ CRI
- DLC (DesignLights Consortium) Qualified see www.designlights.org
- Assembly required
- 1 year warranty, terms and conditions apply

General

Ambient Temp. Range	25 °C
Catalog Number	WBL-204LED

Light Source	LED
Lumens	4584
Mounting Method	Surface;Wall

Electrical Ratings

Lumens Per Watt	124
Wattage	36.9 W

Certifications And Compliance

Certified Listed	UL1598
------------------	--------

Product Assets

- [Brochures - ToolAssistPro Idea Book](#)
- [Catalogs - Tool Assist Pro Ergonomic and Material Handling Products](#)
- [Product Logo - ToolAssistPro-Logo](#)
- [Specifications - WBL-204LED](#)
- [Video - Tool Assist Pro for material handling and ergonomics](#)