



WBL-204LED 48" LED Two Tube Adjustable Workstation Light

By Gleason Reel
Catalog # [WBL-204LED](#)



48" LED Two Tube Adjustable Workstation Light

Features

- 4,000 nominal lumens
- 54,000 hours at LED at L70 for reduced maintenance
- Up to 124 lumens per watt
- Mounts directly to WBL light supports
- 0-10V dimming, standard
- Frosted acrylic lens
- Wide range of applications
- Universal voltage (120 - 277V)
- 80+ CRI
- DLC (DesignLights Consortium) Qualified see www.designlights.org
- Assembly required
- 1 year warranty, terms and conditions apply

General

| | |
|---------------------|--------------|
| Ambient Temp. Range | 25 °C |
| Light Source | LED |
| Lumens | 4584 |
| Mounting Method | Surface;Wall |

Electrical Ratings

| | |
|-----------------|--------|
| Lumens Per Watt | 124 |
| Wattage | 36.9 W |

Certifications And Compliance

| | |
|------------------|--------|
| Certified Listed | UL1598 |
|------------------|--------|

Product Assets

- [Brochures - ToolAssistPro Idea Book](#)
- [Catalogs - Tool Assist Pro Ergonomic and Material Handling Products](#)
- [Product Logo - ToolAssistPro-Logo](#)
- [Video - Tool Assist Pro for material handling and ergonomics](#)



A Hubbell brand