



42" 16K Guy Strain, Clevis / Clevis + 2 Rollers

by CHANCE Utility
Catalog ID: GS16042CC2

42" Fiberglass Guy Strain- 16,000 lb Series- Clevis / Clevis + 2 Rollers



* Representative image

Product Details

General

Description - End Fitting	Clevis - Clevis - 2 Rollers
Strength Rating - Ultimate	16000 lb
Tensile Strength	16000 lb
UPC	096359313175

Dimensions

Diameter - Rod / Tube	0.625 in
Length	42.00 in
Length - Clevis Pin Center to Clevis Bottom	1.38 in
Mounting Bolt Spacing	50.00 in
Weight	3.5 lb

Logistics

Pallet Quantity	320 EA
Standard Package	10

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com