



120" 21K Guy Strain, Clevis / Clevis + 2 Rollers

by CHANCE Utility
Catalog ID: GS21120CC2

120" Fiberglass Guy Strain- 21,000 lb Series- Clevis / Clevis + 2 Rollers



* Representative image

Product Details

General

Description - End Fitting	Clevis - Clevis - 2 Rollers
Strength Rating - Ultimate	21000 lb
Tensile Strength	21000 lb
UPC	096359237419

Dimensions

Diameter - Rod / Tube	0.625 in
Length	120.00 in
Length - Clevis Pin Center to Clevis Bottom	1.4 in
Mounting Bolt Spacing	129.00 in
Weight	7.6 lb

Logistics

Standard Package	1
------------------	---

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com