



# 36" 30K Guy Strain, Clevis / Clevis + 2 Rollers

by CHANCE Utility  
Catalog ID: GS30036CC2

36" Fiberglass Guy Strain- 30,000 lb Series- Clevis / Clevis + 2 Rollers



\* Representative image

## Product Details

### General

Description - End Fitting	Clevis - Clevis - 2 Rollers
Strength Rating - Ultimate	30000 lb
Tensile Strength	30000 lb
UPC	096359495956

### Dimensions

Diameter - Rod / Tube	0.750 in
Length	36.00 in
Length - Clevis Pin Center to Clevis Bottom	2.25 in
Mounting Bolt Spacing	48.00 in
Weight	6.9 lb

### Logistics

Standard Package	1
------------------	---

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsh@hubbell.com](mailto:hpscsh@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)