



120" 30K Guy Strain, Thimble-Eye / Thimble-Eye

by CHANCE Utility
Catalog ID: GS30120PP

120" Fiberglass Guy Strain- 30,000 lb Series- Thimble-Eye / Thimble-Eye



* Representative image

Product Details

General

| | |
|----------------------------|---------------------------|
| Description - End Fitting | Thimble-Eye - Thimble-Eye |
| Strength Rating - Ultimate | 30000 lb |
| Tensile Strength | 30000 lb |
| UPC | 096359578697 |

Dimensions

| | |
|---|-----------|
| Diameter - Rod / Tube | 0.750 in |
| Length | 120.00 in |
| Length - Clevis Pin Center to Clevis Bottom | 3.08 in |
| Mounting Bolt Spacing | 134.00 in |
| Weight | 9.6 lb |

Logistics

| | |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsh@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com